

SWISS TOOLS

Boring bar shank, HSK-T, Shank \varnothing / \varnothing D - A dimension: 63/32-125mm**Order data**

Order number	320102 63/32-125
GTIN	2050001772701
Item class	36D

Description**Version:**

- For efficient turning.
- For left-hand and right-hand turning.

Application:

For mounting exchangeable cutting heads.

Note:

For suitable interchangeable heads see No. 264826 – 264827.

Technical description

Overhang dimension A	125 mm
Shank \varnothing	63 mm
\varnothing D	32 mm
Adapter	HSK-T
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Boring bar base body