



Base body MT shank, without through-coolant, 12×D, Type: 13



Order data

| | |
|--------------|---------------|
| Order number | 232270 13 |
| GTIN | 4045197717917 |
| Item class | 22G |

Description

Note:

Further sizes available on request.

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Reduce feed rates f by 10% and v_c values by 30%.

Through-coolant: no

Number of cutting edges Z : 2

Dia. range D_c : 13 - 17.5 mm

Reach L_1 : 156 mm

Morse taper MT size: 2

Clamping screws: 232990 TX8

Technical description

| | |
|-----------------------------|-----------------|
| Dia. range D_c | 13 - 17.5 mm |
| Reach L_1 | 156 mm |
| Clamping screws | 232990 TX8 |
| Morse taper MT size | 2 |
| Number of cutting edges Z | 2 |
| Version | 12×D |
| Shank | Morse taper |
| Through-coolant | no |
| Type of product | Indexable drill |

Accessories

| | |
|---|------------|
| Torx® set of screws 10 pieces Drive TX8 | 232990 TX8 |
| Torque screwdriver, fixed setting set torque 1,3 N·m | 211750 1,3 |
| PrecisionBit for Torx®, shank E 6.3 Torx® profile TX8 | 674248 TX8 |