



## Base body MT shank, without through-coolant, 1.5xD, Type: 48



### Order data

Order number	232257 48
GTIN	4045197717894
Item class	22G

### Description

#### Version:

For holes up to IT10 accuracy.

#### Straight fluted.

#### Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Further sizes available on request.

Through-coolant: no

Number of cutting edges Z: 2

Dia. range  $D_c$ : 48 - 65 mm

Reach  $L_1$ : 97.5 mm

Morse taper MT size: 5

Clamping screws: 232990 TX20

### Technical description

Reach $L_1$	97.5 mm
Dia. range $D_c$	48 - 65 mm
Clamping screws	232990 TX20
Morse taper MT size	5
Number of cutting edges Z	2
Version	1.5xD
Shank	Morse taper
Through-coolant	no

Type of product	Indexable drill
-----------------	-----------------

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Torx® set of screws 10 pieces Drive TX20	232990 TX20
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600