

SWISS TOOLS

## Cutting head, right-hand, Shank Ø / insert size: 32/11 mm



### Order data

Order number	260316 32/11
GTIN	2050001912305
Item class	29D

### Description

#### Version:

Interchangeable cutting heads for HSK-T and PSC base bodies. Optimum cooling via aligned High Pressure Cooling nozzles.

#### Suitable for :

Boring bar base body **No. 320102; 320103; 320407; 320408.**

Through-coolant: yes

Cutting point / joint: 32 mm

ISO code indexable cutting head: SDUCR/L

suitable indexable insert: DC.. 11T3..

Minimum pre-drill Ø  $D_{min}$ : 40 mm

Centre-line offset: 22 mm

Overall length: 35 mm

### Technical description

Minimum pre-drill Ø $D_{min}$	40 mm
Cutting point / joint	32 mm
ISO code indexable cutting head	SDUCR/L

suitable indexable insert	DC.. 11T3..
Insert size	11 mm
Insert screw	320624_2
Centre-line offset	22 mm
Shank Ø	32 mm
Overall length	35 mm
Insert assignment	left-hand and neutral
Series	Cutting head
Application type	right-hand
Through-coolant	yes

---

## Accessories

Torx-screw No. 2 Type 2	320624 2
-------------------------	----------