

**Garant****Screw-on toolholder, right-hand, Shank / insert size: 25/16mm****Order data**

Order number	260906 25/16
GTIN	4045197713278
Item class	21T

**Technical description**

Shim	269005 7
ISO code toolholder	STGCR/L 2525M16
Shank size	25 mm
Insert size	16 mm
Pack of insert screws	269028 2
suitable indexable insert	TC.. 16T3..
Head length L <sub>1</sub>	23 mm
Functional width L <sub>4</sub>	32 mm
Shim screw	269013 2
Overall length L	150 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 18	269028 18
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim Type 7	269005 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500