

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 16/11mm

Order data

Order number	261353 16/11
GTIN	4045197713643
Item class	21T

Technical description

suitable indexable insert	VC.. 1103..
Pack of insert screws	269028 22
Head length L_1	40 mm
Neck width L_4	11.9 mm
Centre offset L_3	14 mm
Insert size	11 mm
ISO code toolholder	A16M SVVCR/L11
Minimum pre-drill $\varnothing D_{\min}$	23 mm
Overall length L	150 mm
Clamping height L_2	15.5 mm
Setting angle κ	72.5 degrees
Usable depth T	9,5 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500