

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 20/11 mm

Order data

Order number	261353 20/11
GTIN	4045197713650
Item class	21T

Technical description

Insert size	11 mm
ISO code toolholder	A20Q SVVCR/L11
Head length L_1	50 mm
Neck width L_4	13.9 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
suitable indexable insert	VC.. 1103..
Centre offset L_3	14 mm
Pack of insert screws	269028 22
Overall length L	180 mm
Clamping height L_2	19 mm
Setting angle κ	72.5 degrees
Usable depth T	9,5 mm
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500