

**Garant**
**Boring bar steel, right-hand, Shank Ø / insert size: 16/11mm**

**Order data**

Order number	261352 16/11
GTIN	4045197713612
Item class	21T

**Technical description**

Insert size	11 mm
Minimum pre-drill Ø $D_{min}$	23 mm
Head length $L_1$	40 mm
Pack of insert screws	269028 22
suitable indexable insert	VC.. 1103..
ISO code toolholder	A16M SVVCR/L11
Centre offset $L_3$	14 mm
Neck width $L_4$	11.9 mm
Overall length $L$	150 mm
Clamping height $L_2$	15.5 mm
Setting angle $\kappa$	72.5 degrees
Usable depth $T$	9,5 mm
Shank Ø $D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500