

Garant
Screw-on toolholder, left-hand, Shank / insert size: 25/16mm

Order data

Order number	260907 25/16
GTIN	4045197713605
Item class	21T

Technical description

ISO code toolholder	STGCR/L 2525M16
Head length L ₁	23 mm
suitable indexable insert	TC.. 16T3..
Shim screw	269013 2
Pack of insert screws	269028 2
Insert size	16 mm
Shim	269005 7
Functional width L ₄	32 mm
Shank size	25 mm
Overall length L	150 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 7	269005 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws Type 18	269028 18
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500