

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 25/16mm

Order data

Order number	261353 25/16
GTIN	4045197713667
Item class	21T

Technical description

Insert size	16 mm
ISO code toolholder	A25R SVVCR/L16
Centre offset L_3	20 mm
Minimum pre-drill $\varnothing D_{\min}$	34 mm
Pack of insert screws	269028 8
suitable indexable insert	VC.. 1604..
Neck width L_4	19.5 mm
Head length L_1	62.5 mm
Overall length L	200 mm
Clamping height L_2	23 mm
Setting angle κ	72.5 degrees
Usable depth T	13 mm
Shank $\varnothing D_s$	25 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500