



## Swing door cabinet with Plain sheet metal swing doors, Height: 1000mm



### Order data

Order number	949521 1000
GTIN	4062406082024
Item class	92S

### Description

**Version:**

Reinforced doors. DOM twist handle with **cylinder lock**. Storage shelves adjustable at 15 mm intervals.

**Colour:**

Body RAL 7035 light grey. Doors RAL 7016 anthracite **powder-coated**, no special paint colours available.

**Note:**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Usable height	830 mm
Number of shelves	1
Cabinet fronts	Plain sheet metal swing door
Weight	32 kg

Height	1000 mm
Depth	400 mm
Width	930 mm
Material thickness	0.8 mm
Shelf load capacity / maximum distributed shelf load (on metal)	70 kg
Cabinet housing internal load capacity	450 kg
Door opening angle	125 degrees
Height adjustment interval	15 mm
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Filing cabinet

---

## Accessories

Additional storage shelf Type 935	949524 935
Set of storage shelf clips 20 pieces	959011