

HOLEX**Garment locker with fitted base and security twist bar lock, Number of compartments: 2****Order data**

| | |
|--------------|---------------|
| Order number | 949602 2 |
| GTIN | 4062406082079 |
| Item class | 92S |

Description**NOTE: Colour selection possible****Version:**

Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and pressed-in label frame. Choice between plastic feet or fitted base.

With rotary catch; up to size 40 can be locked with padlock (not included).

Ventilation concept: Air entry through holes in the rear of the cabinet floor ensures good ventilation and drying within the compartment. Air infeed for special cabinets with fitted bases is via openings above the recessed base.

Standard:**DIN 4547****Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 7035, RAL 7016, RAL 5005

Height: 1800 mm
 Width: 610 mm
 Depth: 500 mm
 usable width of each compartment: 220 mm
 usable depth of each compartment: 465 mm
 usable height of each clothing compartment: 1270 mm

Technical description

| | |
|--|------------------------------|
| Storage shelf depth | 465 mm |
| Width | 610 mm |
| for padlock | yes |
| Special paints available | no |
| Number of fixed shelves | 1 |
| Weight | 43 kg |
| Height | 1800 mm |
| usable height of each clothing compartment | 1270 mm |
| Ventilation slots in the door | yes |
| Lock version | Security twist bar lock |
| Standard | DIN 4547 |
| usable height of each hat compartment | 345 mm |
| Nameplate | no |
| Shelf width | 220 mm |
| Depth | 500 mm |
| usable depth of each compartment | 465 mm |
| usable width of each compartment | 220 mm |
| Support cabinet version | Fitted base |
| Number of compartments | 2 |
| Number of clothes rails | 1 |
| for padlock with shackle Ø up to | 6 mm |
| Cabinet fronts | Plain sheet metal swing door |
| Sloping roof | no |

| | |
|--------------------|------------------------------|
| Material thickness | 0.8 mm |
| Door opening angle | 110° |
| Colour selection | RAL 7035, RAL 7016, RAL 5005 |
| Type of product | Locker |

Accessories

| | |
|---|------------|
| Clothes hanger pieces 10 | 949775 10 |
| Mirror Type 1 | 949770 1 |
| Padlock galvanised individual keys Type 40 | 085822 40 |
| Precision cylinder lock with tall shackle individual keys Body Ø 40 mm | 085875 40 |
| Additional shelf for shoes Compartment width 300 mm | 949760 300 |
| Plastic tray for shoes Type 1 | 949761 1 |
| Clothes hanger pieces 1 | 949775 1 |