

HOLEX**Garment locker with plastic feet and security twist bar lock, Number of compartments: 2****Order data**

Order number

949604 2

GTIN

Item class

92S

Description**Version:**

Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and pressed-in label frame. Choice between plastic feet or fitted base.

With rotary catch; up to size 40 can be locked with padlock (not included).

Ventilation concept: Air entry through holes in the rear of the cabinet floor ensures good ventilation and drying within the compartment. Air infeed for special cabinets with fitted bases is via openings above the recessed base.

Standard:**DIN 4547****Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

for padlock	yes
Special paints available	no
Number of fixed shelves	1
usable width of each compartment	220 mm
Shelf width	220 mm
Depth	500 mm
Storage shelf depth	465 mm
Number of compartments	2
Lock version	Security twist bar lock
for padlock with shackle Ø up to	6 mm
Ventilation slots in the door	yes
usable depth of each compartment	465 mm
Number of clothes rails	1
Width	610 mm
usable height of each hat compartment	345 mm
Height	1800 mm
Weight	43 kg
usable height of each clothing compartment	1270 mm
Standard	DIN 4547
Support cabinet version	Plastic feet
Sloping roof	no
Cabinet fronts	Plain sheet metal swing door
Nameplate	no
Material thickness	0.8 mm
Door opening angle	110 degrees
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker

Accessories

Additional shelf for shoes Compartment width 300 mm	949760 300
Clothes hanger pieces 10	949775 10
Precision cylinder lock with tall shackle individual keys Body Ø 40 mm	085875 40
Clothes hanger pieces 1	949775 1
Plastic tray for shoes Type 1	949761 1