

HOLEX**Garment locker with plastic feet and security twist bar lock, Number of compartments: 4****Order data**

Order number

949604 4

GTIN

Item class

92S

Description**Version:**

Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and pressed-in label frame. Choice between plastic feet or fitted base.

With rotary catch; up to size 40 can be locked with padlock (not included).

Ventilation concept: Air entry through holes in the rear of the cabinet floor ensures good ventilation and drying within the compartment. Air infeed for special cabinets with fitted bases is via openings above the recessed base.

Standard:**DIN 4547****Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth	500 mm
Weight	77 kg
Sloping roof	no
Standard	DIN 4547
usable height of each clothing compartment	1270 mm
Special paints available	no
Width	1190 mm
Cabinet fronts	Plain sheet metal swing door
Height	1800 mm
Support cabinet version	Plastic feet
for padlock	yes
usable depth of each compartment	465 mm
Lock version	Security twist bar lock
usable height of each hat compartment	345 mm
Shelf width	220 mm
Number of clothes rails	1
Number of compartments	4
Ventilation slots in the door	yes
usable width of each compartment	220 mm
Number of fixed shelves	1
Storage shelf depth	465 mm
Nameplate	no
for padlock with shackle Ø up to	6 mm
Material thickness	0.8 mm
Door opening angle	110 degrees
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker

Accessories

Precision cylinder lock with tall shackle individual keys Body Ø 40 mm	085875 40
Additional shelf for shoes Compartment width 300 mm	949760 300
Clothes hanger pieces 10	949775 10
Plastic tray for shoes Type 1	949761 1
Clothes hanger pieces 1	949775 1