



Garment locker with plastic feet and DOM cylinder lock, Number of compartments: 4



Order data

Order number

949603 4

GTIN

Item class

92S

Description

Version:

Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and pressed-in label frame. Choice between plastic feet or fitted base.

With high-quality cylinder lock.

Ventilation concept: Air entry through holes in the rear of the cabinet floor ensures good ventilation and drying within the compartment. Air infeed for special cabinets with fitted bases is via openings above the recessed base.

Standard:**DIN 4547****Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

usable height of each clothing compartment	1270 mm
Standard	DIN 4547
Special paints available	no
usable height of each hat compartment	345 mm
Depth	500 mm
Cabinet fronts	Plain sheet metal swing door
Storage shelf depth	465 mm
Shelf width	220 mm
Sloping roof	no
Ventilation slots in the door	yes
Height	1800 mm
Number of fixed shelves	1
Nameplate	no
usable depth of each compartment	465 mm
Lock version	Cylinder lock
Number of clothes rails	1
Support cabinet version	Plastic feet
Number of compartments	4
usable width of each compartment	220 mm
Width	1190 mm
Weight	77 kg
Material thickness	0.8 mm
Door opening angle	110°
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker

Accessories

Clothes hanger pieces 1	949775 1
Plastic tray for shoes Type 1	949761 1
Mirror Type 1	949770 1
Clothes hanger pieces 10	949775 10
Additional shelf for shoes Compartment width 300 mm	949760 300