

HOLEX**Garment locker with plastic feet and security twist bar lock, Number of compartments: 3****Order data**

Order number

949604 3

GTIN

Item class

92S

Description**Version:**

Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and pressed-in label frame. Choice between plastic feet or fitted base.

With rotary catch; up to size 40 can be locked with padlock (not included).

Ventilation concept: Air entry through holes in the rear of the cabinet floor ensures good ventilation and drying within the compartment. Air infeed for special cabinets with fitted bases is via openings above the recessed base.

Standard:**DIN 4547****Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Weight	64 kg
Number of compartments	3
Height	1800 mm
Width	900 mm
Support cabinet version	Plastic feet
Special paints available	no
Nameplate	no
Lock version	Security twist bar lock
usable depth of each compartment	465 mm
for padlock with shackle Ø up to	6 mm
Number of clothes rails	1
usable height of each hat compartment	345 mm
Cabinet fronts	Plain sheet metal swing door
for padlock	yes
Number of fixed shelves	1
Standard	DIN 4547
Depth	500 mm
Storage shelf depth	465 mm
Ventilation slots in the door	yes
Sloping roof	no
Shelf width	220 mm
usable width of each compartment	220 mm
usable height of each clothing compartment	1270 mm
Material thickness	0.8 mm
Door opening angle	110°
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker

Accessories

Clothes hanger pieces 10	949775 10
Additional shelf for shoes Compartment width 300 mm	949760 300
Precision cylinder lock with tall shackle individual keys Body Ø 40 mm	085875 40
Plastic tray for shoes Type 1	949761 1
Clothes hanger pieces 1	949775 1
Mirror Type 1	949770 1