



Garment locker with sloping roof, fitted base and DOM cylinder lock, Number of compartments: 4



Order data

Order number

949620 4

GTIN

Item class

92S

Description

Version:

The body has a sloping roof, so that no objects can be placed on top of the locker. Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and pressed-in label frame. Choice between plastic feet or fitted base.

With high-quality cylinder lock.

Standard:**DIN 4547****Colour:**

Body light grey RAL 7035, doors anthracite RAL 7016 **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Shelf width	220 mm
Number of clothes rails	1
usable depth of each compartment	465 mm
Ventilation slots in the door	yes
Depth	500 mm
Sloping roof	yes
Standard	DIN 4547
Height at the front	1800 mm
usable width of each compartment	220 mm
usable height of each hat compartment with sloping roof	360 - 530 mm
suitable for integral helmets	yes
Weight	83 kg
Width	1190 mm
Special paints available	no
Support cabinet version	Fitted base
Height at the rear	2000 mm
Cabinet fronts	Plain sheet metal swing door
usable height of each clothing compartment	1260 mm
Lock version	Cylinder lock
Number of compartments	4
Number of fixed shelves	1
Storage shelf depth	465 mm
Material thickness	0.8 mm
Door opening angle	110 degrees
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker

Accessories

Clothes hanger pieces 1	949775 1
Clothes hanger pieces 10	949775 10