

HOLEX**Garment locker with sloping roof, fitted base and DOM cylinder lock, Number of compartments: 2****Order data**

Order number

949620 2

GTIN

Item class

92S

Description**Version:**

The body has a sloping roof, so that no objects can be placed on top of the locker. Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and pressed-in label frame. Choice between plastic feet or fitted base.

With high-quality cylinder lock.

Standard:**DIN 4547****Colour:**

Body light grey RAL 7035, doors anthracite RAL 7016 **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|---|------------------------------|
| Weight | 49 kg |
| suitable for integral helmets | yes |
| Special paints available | no |
| Depth | 500 mm |
| Height at the rear | 2000 mm |
| Lock version | Cylinder lock |
| usable width of each compartment | 220 mm |
| Sloping roof | yes |
| Shelf width | 220 mm |
| usable height of each clothing compartment | 1260 mm |
| Storage shelf depth | 465 mm |
| Standard | DIN 4547 |
| Number of fixed shelves | 1 |
| Width | 610 mm |
| usable height of each hat compartment with sloping roof | 360 - 530 mm |
| Support cabinet version | Fitted base |
| Number of compartments | 2 |
| Number of clothes rails | 1 |
| Cabinet fronts | Plain sheet metal swing door |
| usable depth of each compartment | 465 mm |
| Height at the front | 1800 mm |
| Ventilation slots in the door | yes |
| Material thickness | 0.8 mm |
| Door opening angle | 110 ° |
| Cylinder lock | modular barrel |
| Colour selection | RAL 7035, RAL 7016, RAL 5005 |
| Type of product | Locker |

Accessories

| | |
|---|------------|
| Clothes hanger pieces 1 | 949775 1 |
| Plastic tray for shoes Type 1 | 949761 1 |
| Clothes hanger pieces 10 | 949775 10 |
| Mirror Type 1 | 949770 1 |
| Additional shelf for shoes Compartment width 300 mm | 949760 300 |