

HOLEX**Garment locker with sloping roof, fitted base and security twist bar lock,
Number of compartments: 2****Order data**

Order number

949621 2

GTIN

Item class

92S

Description**Version:**

The body has a sloping roof, so that no objects can be placed on top of the locker. Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and pressed-in label frame. Choice between plastic feet or fitted base.

With rotary catch; up to size 40 can be locked with padlock (not included).

Standard:**DIN 4547****Colour:**

Body light grey RAL 7035, doors anthracite RAL 7016 **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

usable depth of each compartment	465 mm
Cabinet fronts	Plain sheet metal swing door
Height at the rear	2000 mm
Shelf width	220 mm
for padlock	yes
Lock version	Security twist bar lock
Number of fixed shelves	1
Special paints available	no
Weight	49 kg
Sloping roof	yes
usable width of each compartment	220 mm
Support cabinet version	Fitted base
suitable for integral helmets	yes
Storage shelf depth	465 mm
Number of clothes rails	1
for padlock with shackle Ø up to	6 mm
Height at the front	1800 mm
Width	610 mm
Number of compartments	2
Ventilation slots in the door	yes
Depth	500 mm
Standard	DIN 4547
usable height of each clothing compartment	1260 mm
usable height of each hat compartment with sloping roof	360 - 530 mm
Material thickness	0.8 mm
Door opening angle	110°
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker

Accessories

Additional shelf for shoes Compartment width 300 mm	949760 300
Plastic tray for shoes Type 1	949761 1
Clothes hanger pieces 1	949775 1
Precision cylinder lock with tall shackle individual keys Body Ø 40 mm	085875 40
Mirror Type 1	949770 1
Clothes hanger pieces 10	949775 10