



Garment locker with bench seat and security twist bar lock, Number of compartments: 3



Order data

Order number

949625 3

GTIN

Item class

92S

Description

Version:

Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and pressed-in label frame. Seat slats are normally of beech, approx. 60×35 mm profile, planed all round, rounded at the top, clear varnished. With rotary catch; up to size 40 can be locked with padlock (not included).

Standard:**DIN 4547****Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Height

2090 mm

usable height of each hat compartment	345 mm
Depth	500 mm
Weight	63 kg
Seat bench height	420 mm
usable height of each clothing compartment	1260 mm
usable width of each compartment	230 mm
Seat bench depth	315 mm
usable depth of each compartment	465 mm
Storage shelf depth	465 mm
Shelf width	220 mm
Number of compartments	3
Width	900 mm
Material thickness	0.8 mm
Door opening angle	110 degrees
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker

Accessories

Precision cylinder lock with tall shackle individual keys Body Ø 40 mm	085875 40
Plastic tray for shoes Type 1	949761 1
Additional shelf for shoes Compartment width 300 mm	949760 300
Clothes hanger pieces 10	949775 10
Clothes hanger pieces 1	949775 1