



Garment locker with sloping roof, bench seat and DOM cylinder lock, Number of compartments: 3



Order data

Order number

949640 3

GTIN

Item class

92S

Description

Version:

The body has a sloping roof, so that no objects can be placed on top of the locker. Compartment width 300 mm with welded-in hat shelf. The hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and pressed-in label frame. Seat slats on the bench seat are normally of beech, approx. 60×35 mm profile, planed all round, rounded at the top, clear varnished.

With high-quality cylinder lock.

Standard:**DIN 4547****Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite, seat similarly anthracite grey, **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth	500 mm
Weight	83 kg
Seat bench height	420 mm
Seat bench width	900 mm
usable height of each hat compartment with sloping roof	360 - 530 mm
Seat bench depth	315 mm
Width	900 mm
usable width of each compartment	220 mm
Height at the rear	2290 mm
usable height of each clothing compartment	1260 mm
Height at the front	2090 mm
usable depth of each compartment	465 mm
Material thickness	0.8 mm
Door opening angle	110 °
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker

Accessories

Mirror Type 1	949770 1
Additional shelf for shoes Compartment width 300 mm	949760 300
Clothes hanger pieces 10	949775 10
Clothes hanger pieces 1	949775 1
Plastic tray for shoes Type 1	949761 1