



Garment locker with sloping roof, bench seat and security twist bar lock, Number of compartments: 3



Order data

Order number

949641 3

GTIN

Item class

92S

Description

Version:

The body has a sloping roof, so that no objects can be placed on top of the locker. Compartment width 300 mm with welded-in hat shelf. The hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and pressed-in label frame. Seat slats on the bench seat are normally of beech, approx. 60×35 mm profile, planed all round, rounded at the top, clear varnished.

With rotary catch; up to size 40 can be locked with padlock (not included).

Standard:**DIN 4547****Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite, seat similarly anthracite grey, **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Storage shelf depth	465 mm
Weight	83 kg
Height at the front	2090 mm
usable depth of each compartment	465 mm
Height at the rear	2290 mm
Seat bench depth	315 mm
Depth	500 mm
Width	900 mm
Shelf width	220 mm
Seat bench width	900 mm
usable height of each clothing compartment	1260 mm
usable width of each compartment	220 mm
Seat bench height	420 mm
usable height of each hat compartment with sloping roof	360 - 530 mm
Material thickness	0.8 mm
Door opening angle	110 °
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker

Accessories

Precision cylinder lock with tall shackle individual keys Body Ø 40 mm	085875 40
Plastic tray for shoes Type 1	949761 1
Clothes hanger pieces 1	949775 1
Additional shelf for shoes Compartment width 300 mm	949760 300
Mirror Type 1	949770 1
Clothes hanger pieces 10	949775 10