



Garment locker with bench seat and security twist bar lock, Number of compartments: 4



Order data

Order number	949625 4
GTIN	4062406082338
Item class	92S

Description

NOTE: Colour selection possible

Version:

Compartment width 300 mm with welded-in hat shelf. Hanger rail has 3 sliding clothes hooks. Door with diamond pattern ventilation holes and pressed-in label frame. Seat slats are normally of beech, approx. 60×35 mm profile, planed all round, rounded at the top, clear varnished. With rotary catch; up to size 40 can be locked with padlock (not included).

Standard:

DIN 4547

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 7035, RAL 7016, RAL 5005

Height: 2090 mm

Width: 1190 mm

Depth: 500 mm

usable width of each compartment: 230 mm
 usable depth of each compartment: 465 mm
 usable height of each clothing compartment: 1260 mm

Technical description

Seat bench height	420 mm
usable width of each compartment	230 mm
usable depth of each compartment	465 mm
Weight	80 kg
Height	2090 mm
Shelf width	220 mm
usable height of each hat compartment	345 mm
Depth	500 mm
Storage shelf depth	465 mm
usable height of each clothing compartment	1260 mm
Seat bench depth	315 mm
Width	1190 mm
Number of compartments	4
Material thickness	0.8 mm
Door opening angle	110°
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker

Accessories

Clothes hanger pieces 1	949775 1
Additional shelf for shoes Compartment width 300 mm	949760 300
Plastic tray for shoes piece 1	949761 1
Precision cylinder lock with tall shackle individual keys Body Ø 40 mm	085875 40

Mirror pieces 1	949770 1
Clothes hanger pieces 10	949775 10
Padlock galvanised individual keys Type 40	085822 40