



Garment locker with base and sloping roof, for black-white separation and security twist bar lock, Number of compartments: 2



Order data

Order number

949712 2

GTIN

Item class

92S

Description

Version:

Garment locker with extra wide split compartment, for black-white separation. The partition within a compartment is for hygienic separation of street clothes and work clothes. The two swing doors close to each other and are centrally locked with a single lock. Type of garment locker as described under No. 949620.

With rotary catch; up to size 40 can be locked with padlock (not included).

Standard:**DIN 4547****Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**. No special paint finishes available.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Shelf width	220 mm
Height at the front	1800 mm
Height at the rear	2000 mm
usable width of each compartment	2 × 240 mm
usable depth of each compartment	465 mm
usable height of each clothing compartment	1260 mm
Width	610 mm
Depth	500 mm
Weight	49 kg
Storage shelf depth	465 mm
usable height of each hat compartment with sloping roof	360 - 530 mm
Material thickness	0.8 mm
Door opening angle	110°
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Locker

Accessories

Additional shelf for shoes Compartment width 300 mm	949760 300
Clothes hanger pieces 1	949775 1
Clothes hanger pieces 10	949775 10
Precision cylinder lock with tall shackle individual keys Body Ø 40 mm	085875 40
Plastic tray for shoes Type 1	949761 1
Mirror Type 1	949770 1