



Combination grinding disc PREMIUM*** CUT AND GRIND, Disc Ø: 125mm



Order data

Order number	563220 125
GTIN	9003170019156
Item class	53T

Description

Version:

Thin **combination grinding disc** with multi-layer structure for high stability, with depth-of-cut protection in the dished area.

Application:

For separation and light metal-removal grinding without changing tools.

Specification:

A46Q-BFXA.

Technical description

Bore Ø	22.23 mm
maximum speed	12200 min ⁻¹
Disc thickness	2 mm
Shape description	depressed centre
Specification	A46Q-BFXA
Disc Ø	125 mm

for material thicknesses	6 - 10 mm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
recommended approach angle	20-30 degrees
recommended approach angle	90 degrees
optimised for material	Steel
optimised for material	HSS
Propulsive equipment	Angle grinders
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
dry	suitable		