

**Garant**
**HiPer-Drill cutter insert m7, HB7725, Ø D: 23,5 mm**

**Order data**

Order number	231660 23,5
GTIN	4045197714541
Item class	21M

**Description**
**Version:**

Vee ground cutter inserts for precise positioning and stable seating.  
Concentricity when assembled  $\leq 20 \mu\text{m}$ . For holes up to IT9 accuracy.

**Note:**

Further sizes available on request. Cutting data apply to 5×D drilling bodies.  
Use exclusively cutter heads of the same type when drilling pilot holes.  
for base body Ø D: 23 mm  
Feed f in grey cast iron (G): 0.4 mm/rev.

**Technical description**

Ø D	23.5 mm
for base body Ø D	23 mm
Feed f in grey cast iron (G)	0.4 mm/rev.
Number of changes/inserts	1
Grade	HB7725

Tool material	Carbide
Point angle	135 degrees
Number of cutting edges Z	2
Type of product	Cutter insert for boring