

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 25/12mm

Order data

| | |
|--------------|---------------|
| Order number | 250034 25/12 |
| GTIN | 4062406082949 |
| Item class | 21U |

Technical description

| | |
|--|-------------------------------|
| ISO code toolholder | A25X DCLNR/L12 |
| Setting angle κ | 95 degrees |
| Insert size | 12 mm |
| Centre offset L_3 | 17 mm |
| Shim | 259033 2 |
| Minimum pre-drill $\varnothing D_{\min}$ | 29.5 mm |
| Shim screw | 259027 2 |
| Overall length L | 225 mm |
| Clamping height L_2 | 24.3 mm |
| suitable indexable insert | CN.. 1204.. |
| Clamp, screw, O-ring | 259036 1 |
| Shank $\varnothing D_s$ | 25 mm |
| Standard | Works standard |
| Application type | right-hand |
| Boring depth up to | 3xD |
| Through-coolant | yes |
| Application | Internal longitudinal turning |

Type of product

Boring bar