

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 32/12mm**

**Order data**

Order number	250034 32/12
GTIN	4062406082956
Item class	21U

**Technical description**

ISO code toolholder	A32X DCLNR/L12
Overall length L	288 mm
Minimum pre-drill $\varnothing D_{\min}$	38 mm
Centre offset $L_3$	22 mm
Shim screw	259027 2
Setting angle $\kappa$	95 degrees
suitable indexable insert	CN.. 1204..
Insert size	12 mm
Shim	259033 2
Clamping height $L_2$	31 mm
Clamp, screw, O-ring	259036 1
Shank $\varnothing D_s$	35 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar