

Garant
Boring bar, steel, left-hand, Shank \varnothing / insert size: 25/12mm

Order data

Order number	250035 25/12
GTIN	4062406082963
Item class	21U

Technical description

Centre offset L_3	17 mm
Minimum pre-drill $\varnothing D_{\min}$	29.5 mm
suitable indexable insert	CN.. 1204..
ISO code toolholder	A25X DCLNR/L12
Shim screw	259027 2
Insert size	12 mm
Setting angle κ	95 degrees
Shim	259033 2
Clamping height L_2	24.3 mm
Overall length L	225 mm
Clamp, screw, O-ring	259036 1
Shank $\varnothing D_s$	25 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar