

Garant GRIDLINE

**Workbench, left side open, right side 4 drawers, Bamboo worktop, 20×20G,  
Worktop length: 1500mm****Order data**

Order number	921001 1500
GTIN	4062406082802
Item class	9GG

**Description****Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Feet with plastic pads, do not damage the floor.

Recessed open housing for ergonomic posture.

Drawer bodies always RAL 7035 light grey, **powder coated**. Variable colours for the drawer fronts. No surrounding ledges, thereby allowing optimum cleaning and full availability of the area for drawer dividers (boxes, rigid foam inlays, slotted partitions). Drawer runner mountings at 25 mm intervals.

Locking system with 5-pin cylinder locks and modular barrels. Compatible with integrated locking systems.

**Fitted with:**

Drawer front height (right) mm: 75, 100, 150, 200

**Optional extras:**

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated**. **Drawer body not configurable, always RAL 7035 light grey.**

**Technical description**

Weight	125.6 kg
Worktop length	1500 mm
Support cabinet depth	700 mm
Drawer body usable height	525 mm
Height	850 mm
Drawer usable width	500 mm
Drawer usable width in G	20
Series	Ready-to-go
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Number of drawers	4
Support cabinet width	1300 mm
Worktop depth	750 mm
Drawer usable depth in G	20
Drawer usable area in G	20×20
Worktop thickness	50 mm
Drawer usable depth	500 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

## Accessories

Workshop set Number of tools 26	955081 26
Lock plate for GridLine Type KO21	914227 KO21
easyPick small parts storage bins set Drawer front height / type 75/2	950300 75/2
easyPick small parts storage bins set Drawer front height / type 75/1	950300 75/1
Drawer Drawer front height 100 mm	927800 100
Marking out and sawing Number of tools 8	954895 8
Mat for drawers Dimension in G 20X20	951830 20X20
Combination spanner set Number of tools 20	952505 20
Pliers set Number of tools 5	954305 5
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20
Non-slip mats set for drawers,5 pieces Dimension in G 20X20	951885 20X20
easyPick small parts storage bins set Drawer front height / type 75/3	950300 75/3
Socket set 1/2 inch Number of tools 32	953821 32
Drawer Drawer front height 200 mm	927800 200
Slotted dividers / plain dividers set Drawer front height / type 150/5	950320 150/5
Disassembly tool Type 1	950070 1
Socket set 1/4 inch and 1/2 inch Number of tools 37	953828 37
Slotted dividers / plain dividers set Drawer front height / type 100/1	950320 100/1
Slotted dividers / plain dividers set Drawer front height / type 100/3	950320 100/3
Pliers set Number of tools 5	954295 5
Slotted dividers / plain dividers set Drawer front height / type 75/1	950320 75/1
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75

Slotted dividers / plain dividers set Drawer front height / type 150/4	950320 150/4
Slotted dividers / plain dividers set Drawer front height / type 100/2	950320 100/2
Drawer Drawer front height 150 mm	927800 150
Screwdriver set Number of tools 10	953521 10
Socket set 1/4 inch and 1/2 inch Number of tools 39	953833 39
Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Slotted dividers / plain dividers set Drawer front height / type 75/2	950320 75/2
Cleaner and care oil set Type 1	926403 1
File set Number of tools 6	952253 6
Slotted dividers / plain dividers set Drawer front height / type 75/3	950320 75/3
Drawer Drawer front height 75 mm	927800 75
Workshop set Number of tools 22	955071 22
Pliers set Number of tools 5	954306 5
Screwdriver set Number of tools 10	953522 10
Workshop set Number of tools 22	955072 22