

Garant GRIDLINE

Workbench, 9 drawers, Bamboo worktop, 20×20G, Worktop length: 1500mm**Order data**

Order number	921091 1500
GTIN	4062406083052
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Feet with plastic pads, do not damage the floor.

Drawer bodies always RAL 7035 light grey, **powder coated**. Variable colours for the drawer fronts. No surrounding ledges, thereby allowing optimum cleaning and full availability of the area for drawer dividers (boxes, rigid foam inlays, slotted partitions). Drawer runner mountings at 25 mm intervals.

Locking system with 5-pin cylinder locks and modular barrels. Compatible with integrated locking systems.

Fitted with:

Drawer front height (left) mm: 75, 75, 100, 125, 250

Drawer front height (right) mm: 75, 100, 200, 250

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated**. **Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Drawer usable width in G	20
--------------------------	----

Support cabinet depth	700 mm
Support cabinet width	1300 mm
Worktop thickness	50 mm
Weight	181.7 kg
Drawer usable depth	500 mm
Series	Ready-to-go
Drawer usable width	500 mm
Worktop depth	750 mm
Drawer usable depth in G	20
Worktop length	1500 mm
Height	950 mm
Number of drawers	4
Drawer usable area in G	20×20
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer body usable height	625 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Workshop set Number of tools 22	955071 22
Drawer Drawer front height 125 mm	927800 125
Drawer Drawer front height 75 mm	927800 75
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Slotted dividers / plain dividers set Drawer front height / type 100/2	950320 100/2
Screwdriver set Number of tools 10	953521 10
Slotted dividers / plain dividers set Drawer front height / type 150/5	950320 150/5
Slotted dividers / plain dividers set Drawer front height / type 100/1	950320 100/1
Combination spanner set Number of tools 20	952505 20
Drawer Drawer front height 250 mm	927800 250
Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Workshop set Number of tools 26	955081 26
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20
Slotted dividers / plain dividers set Drawer front height / type 75/2	950320 75/2
Socket set 1/4 inch and 1/2 inch Number of tools 37	953828 37
Slotted dividers / plain dividers set Drawer front height / type 150/4	950320 150/4
Socket set 1/4 inch and 1/2 inch Number of tools 39	953833 39
Disassembly tool Type 1	950070 1
Marking out and sawing Number of tools 8	954895 8
Lock plate for GridLine Type KO21	914227 KO21
easyPick small parts storage bins set Drawer front height / type 75/1	950300 75/1
Slotted dividers / plain dividers set Drawer front height / type 125/4	950320 125/4
Socket set 1/2 inch Number of tools 32	953821 32

Overlay of plasticised PVC transparent Width 1500 mm	951951 1500
Pliers set Number of tools 5	954305 5
Slotted dividers / plain dividers set Drawer front height / type 125/3	950320 125/3
Pliers set Number of tools 5	954295 5
Slotted dividers / plain dividers set Drawer front height / type 75/1	950320 75/1
Slotted dividers / plain dividers set Drawer front height / type 100/3	950320 100/3
Non-slip mats set for drawers,5 pieces Dimension in G 20X20	951885 20X20
Cleaner and care oil set Type 1	926403 1
easyPick small parts storage bins set Drawer front height / type 75/2	950300 75/2
Slotted dividers / plain dividers set Drawer front height / type 125/6	950320 125/6
File set Number of tools 6	952253 6
easyPick small parts storage bins set Drawer front height / type 75/3	950300 75/3
Slotted dividers / plain dividers set Drawer front height / type 75/3	950320 75/3
Slotted dividers / plain dividers set Drawer front height / type 125/1	950320 125/1
Drawer Drawer front height 100 mm	927800 100
Mat for drawers Dimension in G 20X20	951830 20X20
Screwdriver set Number of tools 10	953522 10
Pliers set Number of tools 5	954306 5
Workshop set Number of tools 22	955072 22