

Garant GRIDLINE

**Vario Basic workbench with rear panel, height 850 mm, Bamboo worktop,
Worktop length: 1000mm****Order data**

Order number	922021 1000
GTIN	4062406083144
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. Additional rear panel to increase the load capacity. With 1 × pair of stabilising plates for stiffening.

Supplied with:

2 × support legs, 1 × pair of stabilising plates, 1 × two-piece rear panel, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Body and supports light grey RAL 7035, **powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Material of worktop	Bamboo
Worktop length	1000 mm
Weight	50 kg

Worktop thickness	50 mm
Height	850 mm
Series	vario Basic
Worktop depth	750 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Workbench/desk load capacity - maximum distributed load (on wood)	600 kg
Insert thickness	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

Accessories

Rear panel / storage shelf single-piece suitable for worktop length 1000 mm	927140 1000
Worktop thickness 50 mm of bamboo strips glued cross-wise Worktop length 1000 mm	926001 1000
Support leg Height 800 mm	927000 800
Stabilising plate Type 1	927122 1