

Garant GRIDLINE

Vario Basic workbench with rear panel, height 850 mm, Beech marine ply worktop, Worktop length: 1500mm**Order data**

Order number	922024 1500
GTIN	4062406083182
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. Additional rear panel to increase the load capacity. With 1 × pair of stabilising plates for stiffening.

Supplied with:

2 × support legs, 1 × pair of stabilising plates, 1 × two-piece rear panel, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Body and supports light grey RAL 7035, **powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Series	vario Basic
Worktop length	1500 mm
Height	850 mm
Weight	68 kg

Worktop thickness	50 mm
Worktop depth	750 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Workbench/desk load capacity - maximum distributed load (on wood)	600 kg
Insert thickness	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

Accessories

Support leg Height 800 mm	927000 800
Rear panel / storage shelfsingle-piece suitable for worktop length 1500 mm	927140 1500
Worktop thickness 50 mmof beech marine ply Worktop length 1500 mm	926081 1500
Stabilising plate Type 1	927122 1