

Garant GRIDLINE

**Vario Basic workbench with rear panel, height 850 mm, Bamboo worktop,  
Worktop length: 2000mm****Order data**

Order number	922021 2000
GTIN	4062406083168
Item class	9GG

**Description****Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. Additional rear panel to increase the load capacity. With 1 × pair of stabilising plates for stiffening.

**Supplied with:**

2 × support legs, 1 × pair of stabilising plates, 1 × two-piece rear panel, worktop.

**Optional extras:**

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

**Colour:**

Body and supports light grey RAL 7035, **powder-coated.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Series	vario Basic
Height	850 mm
Weight	86 kg
Material of worktop	Bamboo
Worktop thickness	50 mm

Worktop length	2000 mm
Worktop depth	750 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Workbench/desk load capacity - maximum distributed load (on wood)	600 kg
Insert thickness	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

---

## Accessories

Support leg Height 800 mm	927000 800
Rear panel / storage shelfsingle-piece suitable for worktop length 2000 mm	927140 2000
Stabilising plate Type 1	927122 1
Worktop thickness 50 mmof bamboo strips glued cross-wise Worktop length 2000 mm	926001 2000