

Garant GRIDLINE

**Vario Basic workbench with rear panel, height 850 mm, Beech marine ply worktop, Worktop length: 2000mm****Order data**

Order number	922024 2000
GTIN	4062406083199
Item class	9GG

**Description****Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. Additional rear panel to increase the load capacity. With 1 × pair of stabilising plates for stiffening.

**Supplied with:**

2 × support legs, 1 × pair of stabilising plates, 1 × two-piece rear panel, worktop.

**Optional extras:**

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

**Colour:**

Body and supports light grey RAL 7035, **powder-coated.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Weight	86 kg
Series	vario Basic
Worktop depth	750 mm
Worktop thickness	50 mm
Height	850 mm

Worktop length	2000 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Workbench/desk load capacity - maximum distributed load (on wood)	600 kg
Insert thickness	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

## Accessories

Stabilising plate Type 1	927122 1
Rear panel / storage shelvesingle-piece suitable for worktop length 2000 mm	927140 2000
Worktop thickness 50 mmof beech marine ply Worktop length 2000 mm	926081 2000
Support leg Height 800 mm	927000 800