

Garant GRIDLINE

**Vario Basic workbench with rear panel, height 950 mm, Bamboo worktop,
Worktop length: 1500mm****Order data**

Order number	922031 1500
GTIN	4062406083243
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. Additional rear panel to increase the load capacity. With 1 × pair of stabilising plates for stiffening.

Supplied with:

2 × support legs, 1 × pair of stabilising plates, 1 × two-piece rear panel, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Body and supports light grey RAL 7035, **powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Worktop length	1500 mm
Weight	69 kg
Worktop depth	750 mm
Worktop thickness	50 mm

Height	950 mm
Material of worktop	Bamboo
Series	vario Basic
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Workbench/desk load capacity - maximum distributed load (on wood)	600 kg
Insert thickness	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Work table

Accessories

Stabilising plate Type 1	927122 1
Worktop thickness 50 mm of bamboo strips glued cross-wise Worktop length 1500 mm	926001 1500
Rear panel / storage shelf single-piece suitable for worktop length 1500 mm	927140 1500
Support leg Height 900 mm	927000 900