

Garant GRIDLINE

**Vario workbench with drawer casing 16G, height 850 mm, Eluplan worktop, dark, 12×20G, Worktop length: 2000/2mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 922047 2000/2 |
| GTIN         | 4062406083489 |
| Item class   | 9GG           |

**Description****Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer cabinet 16G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

**Fitted with:**

Drawer front height, mm: 75#150

**Supplied with:**

2 × support legs, 1 × pair of stabilising plates, drawer cabinet with drawers, worktop.

**Optional extras:**

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

**Colour:**

Cabinet body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

|                          |       |
|--------------------------|-------|
| Drawer usable width in G | 12    |
| Drawer usable area in G  | 12×20 |

|                                                                   |                                                                |
|-------------------------------------------------------------------|----------------------------------------------------------------|
| Drawer body height                                                | 300 mm                                                         |
| Height                                                            | 850 mm                                                         |
| Drawer body depth                                                 | 650 mm                                                         |
| Worktop depth                                                     | 750 mm                                                         |
| Worktop length                                                    | 2000 mm                                                        |
| Weight                                                            | 96 kg                                                          |
| Drawer body usable height                                         | 225 mm                                                         |
| Drawer usable width                                               | 300 mm                                                         |
| Worktop thickness                                                 | 50 mm                                                          |
| Drawer usable depth in G                                          | 20                                                             |
| Number of drawers                                                 | 2                                                              |
| Drawer usable depth                                               | 500 mm                                                         |
| Workbench/desk load capacity - maximum distributed load (on wood) | 400 kg                                                         |
| Series                                                            | vario                                                          |
| Drawer body width                                                 | 400 mm                                                         |
| Design version                                                    | Steel hollow section construction                              |
| Material thickness                                                | 1 mm                                                           |
| Workbench height                                                  | 850 mm                                                         |
| Drawer/pull-out shelf load capacity                               | 75 kg                                                          |
| Insert thickness                                                  | 50 mm                                                          |
| Drawer runner extension (partial/full extension)                  | 100 %                                                          |
| Cylinder lock                                                     | modular lock barrel                                            |
| Colour selection                                                  | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute                                            | 12×20G                                                         |
| Type of product                                                   | Workbench                                                      |

## Accessories

|                                                                         |              |
|-------------------------------------------------------------------------|--------------|
| Lock barrel with 2 keys Lock number Ho (3-digit) 003                    | 950050 003   |
| Drawer Drawer front height 150 mm                                       | 927500 150   |
| Drawer Drawer front height 75 mm                                        | 927500 75    |
| Lock plate for GridLine Type KO21                                       | 914227 KO21  |
| Worktop with dark grey plastic coating (Eluplan) Worktop length 2000 mm | 926241 2000  |
| Support leg Height 800 mm                                               | 927000 800   |
| Stabilising plate Type 1                                                | 927122 1     |
| Drawer casing 16G with drawers Height / number of drawers 300/2         | 927300 300/2 |