

Garant GRIDLINE

Vario workbench with drawer casing 16G, height 850 mm, Beech marine ply worktop, 12×20G, Worktop length: 1000/2mm**Order data**

| | |
|--------------|---------------|
| Order number | 922044 1000/2 |
| GTIN | 4062406083380 |
| Item class | 9GG |

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer cabinet 16G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height, mm: 75#150

Supplied with:

2 × support legs, 1 × pair of stabilising plates, drawer cabinet with drawers, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

| | |
|---|--|
| Worktop depth | 750 mm |
| Drawer body depth | 650 mm |
| Drawer usable width in G | 12 |
| Drawer usable depth | 500 mm |
| Number of drawers | 2 |
| Drawer body width | 400 mm |
| Drawer body usable height | 225 mm |
| Series | vario |
| Drawer usable width | 300 mm |
| Worktop thickness | 50 mm |
| Drawer usable depth in G | 20 |
| Weight | 68 kg |
| Drawer body height | 300 mm |
| Height | 850 mm |
| Drawer usable area in G | 12×20 |
| Workbench/desk load capacity - maximum distributed load (on wood) | 400 kg |
| Worktop length | 1000 mm |
| Design version | Steel hollow section construction |
| Material thickness | 1 mm |
| Workbench height | 850 mm |
| Drawer/pull-out shelf load capacity | 75 kg |
| Insert thickness | 50 mm |
| Drawer runner extension (partial/full extension) | 100 % |
| Cylinder lock | modular lock barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute | 12×20G |
| Type of product | Workbench |

Accessories

| | |
|--|--------------|
| Lock plate for GridLine Type KO21 | 914227 KO21 |
| Drawer Drawer front height 150 mm | 927500 150 |
| Drawer Drawer front height 75 mm | 927500 75 |
| Lock barrel with 2 keys Lock number Ho (3-digit) 003 | 950050 003 |
| Support leg Height 800 mm | 927000 800 |
| Worktop thickness 50 mm of beech marine ply Worktop length 1000 mm | 926081 1000 |
| Stabilising plate Type 1 | 927122 1 |
| Drawer casing 16G with drawers Height / number of drawers 300/2 | 927300 300/2 |