

Garant GRIDLINE

Vario workbench with drawer casing 16G, height 850 mm, Bamboo worktop, 12x20G, Worktop length: 1500/3mm



Order data

Order number	922041 1500/3
GTIN	4062406083359
Item class	9GG

Description

Version:

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer cabinet 16G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height, mm: 75, 100, 150

Supplied with:

2 x support legs, 1 x pair of stabilising plates, drawer cabinet with drawers, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Drawer usable depth	500 mm
Drawer usable width in G	12

Drawer body usable height	325 mm
Drawer body height	400 mm
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Drawer body depth	650 mm
Worktop depth	750 mm
Worktop thickness	50 mm
Height	850 mm
Number of drawers	3
Series	vario
Weight	92 kg
Worktop length	1500 mm
Drawer usable width	300 mm
Drawer body width	400 mm
Drawer usable area in G	12×20
Drawer usable depth in G	20
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12×20G
Type of product	Workbench

Accessories

Drawer Drawer front height 100 mm	927500 100
Lock plate for GridLine Type KO21	914227 KO21
Cleaner and care oil set Type 1	926403 1
Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Drawer Drawer front height 150 mm	927500 150
Drawer Drawer front height 75 mm	927500 75
Drawer casing 16G with drawers Height / number of drawers 400/3	927300 400/3
Stabilising plate Type 1	927122 1
Support leg Height 800 mm	927000 800