

Garant GRIDLINE

Vario workbench with drawer casing 16G, height 950 mm, Eluplan worktop, dark, 12×20G, Worktop length: 1500/3mm**Order data**

Order number	922057 1500/3
GTIN	4062406083656
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer casing 16G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height, mm: 75, 100, 150

Supplied with:

2 × support legs, 1 × pair of stabilising plates, drawer casing with drawers, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Drawer usable width	300 mm
---------------------	--------

Drawer usable area in G	12×20
Drawer usable depth in G	20
Worktop depth	750 mm
Drawer usable width in G	12
Drawer body width	400 mm
Number of drawers	3
Drawer usable depth	500 mm
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Worktop length	1500 mm
Drawer body depth	650 mm
Series	vario
Drawer body height	400 mm
Weight	93 kg
Worktop thickness	50 mm
Drawer body usable height	325 mm
Height	950 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12×20G
Type of product	Workbench

Accessories

Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 150 mm	927500 150
Drawer Drawer front height 75 mm	927500 75
Drawer Drawer front height 100 mm	927500 100
Support leg Height 900 mm	927000 900
Drawer casing 16G with drawers Height / number of drawers 400/3	927300 400/3
Worktop with dark grey plastic coating (Eluplan) Worktop length 1500 mm	926241 1500
Stabilising plate Type 1	927122 1