

Garant GRIDLINE

Vario workbench with drawer casing 16G, height 950 mm, Beech marine ply worktop, 12×20G, Worktop length: 2000/2mm**Order data**

Order number	922054 2000/2
GTIN	4062406083601
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer casing 16G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height, mm: 75#150

Supplied with:

2 × support legs, 1 × pair of stabilising plates, drawer casing with drawers, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Worktop depth	750 mm
Drawer usable width in G	12

Drawer body usable height	225 mm
Drawer usable depth	500 mm
Worktop thickness	50 mm
Drawer usable width	300 mm
Height	950 mm
Number of drawers	2
Drawer body height	300 mm
Worktop length	2000 mm
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Drawer usable depth in G	20
Drawer body width	400 mm
Series	vario
Weight	97 kg
Drawer body depth	650 mm
Drawer usable area in G	12×20
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12×20G
Type of product	Workbench

Accessories

Stabilising plate Type 1	927122 1
Support leg Height 900 mm	927000 900
Drawer casing 16G with drawers Height / number of drawers 300/2	927300 300/2
Worktop thickness 50 mm of beech marine ply Worktop length 2000 mm	926081 2000