

Garant GRIDLINE

Vario workbench with drawer casing 24G, height 850 mm, Beech marine ply worktop, 20×20G, Worktop length: 2000mm**Order data**

Order number	922524 2000
GTIN	4062406084097
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer cabinet 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height, mm: 125

Supplied with:

2 × support legs, 1 × pair of stabilising plates, drawer cabinet with drawers, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Worktop thickness	50 mm
Drawer usable depth in G	20

Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Drawer body width	600 mm
Drawer usable area in G	20×20
Drawer body depth	650 mm
Worktop length	2000 mm
Worktop depth	750 mm
Series	vario
Drawer usable width in G	20
Drawer body height	200 mm
Weight	116 kg
Number of drawers	1
Drawer usable width	500 mm
Height	850 mm
Drawer body usable height	125 mm
Drawer usable depth	500 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 125 mm	927800 125
Drawer casing 24G with drawers Height / number of drawers 200/1	927600 200/1
Worktop thickness 50 mm of beech marine ply Worktop length 2000 mm	926081 2000
Stabilising plate Type 1	927122 1
Support leg Height 800 mm	927000 800