

Garant GRIDLINE

Vario workbench with drawer casing 24G, height 950 mm, Bamboo worktop, 20×20G, Worktop length: 1000mm**Order data**

Order number	922531 1000
GTIN	4062406084134
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer cabinet 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height, mm: 125

Supplied with:

2 × support legs, 1 × pair of stabilising plates, drawer cabinet with drawers, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Drawer usable depth	500 mm
Worktop thickness	50 mm
Worktop length	1000 mm
Drawer body usable height	125 mm
Worktop depth	750 mm
Drawer usable width in G	20
Drawer usable depth in G	20
Drawer usable area in G	20×20
Weight	88 kg
Drawer body width	600 mm
Number of drawers	1
Drawer usable width	500 mm
Height	950 mm
Drawer body depth	650 mm
Drawer body height	200 mm
Series	vario
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 125 mm	927800 125
Support leg Height 900 mm	927000 900
Stabilising plate Type 1	927122 1
Drawer casing 24G with drawers Height / number of drawers 200/1	927600 200/1
Worktop thickness 50 mm of bamboo strips glued cross-wise Worktop length 1000 mm	926001 1000