

Garant GRIDLINE

Vario workbench with drawer casing 16G, height 950 mm, Bamboo worktop, 12x20G, Worktop length: 1500/6mm**Order data**

Order number	922131 1500/6
GTIN	4062406083823
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer cabinet 16G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height, mm: 75, 100, 100, 125, 150, 250

Supplied with:

1 × support leg, 1 × pair of stabilising plates, drawer cabinet with drawers, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Drawer usable width in G	12
--------------------------	----

Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer body width	400 mm
Worktop depth	750 mm
Drawer usable depth	500 mm
Worktop length	1500 mm
Worktop thickness	50 mm
Series	vario
Number of drawers	6
Drawer usable width	300 mm
Weight	121 kg
Drawer body usable height	800 mm
Height	950 mm
Drawer usable area in G	12×20
Drawer body depth	650 mm
Drawer usable depth in G	20
Drawer body height	900 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12×20G
Type of product	Workbench

Accessories

Drawer Drawer front height 150 mm	927500 150
Drawer Drawer front height 100 mm	927500 100
Drawer Drawer front height 125 mm	927500 125
Drawer Drawer front height 75 mm	927500 75
Drawer Drawer front height 250 mm	927500 250
Lock plate for GridLine Type KO21	914227 KO21
Drawer casing 16G with drawers Height / number of drawers 900/6	927300 900/6
Worktop thickness 50 mm of bamboo strips glued cross-wise Worktop length 1500 mm	926001 1500
Stabilising plate Type 1	927122 1
Support leg Height 900 mm	927000 900