


Garant GRIDLINE

**Vario workbench with drawer casing 24G, height 850 mm, Beech marine ply worktop, 20×20G, Worktop length: 2000/3mm****Order data**

Order number	922624 2000/3
GTIN	4062406084455
Item class	9GG

**Description****Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

**Fitted with:**

Drawer front height, mm: 50, 75, 100

**Supplied with:**

2 × support legs, 1 × pair of stabilising plates, drawer casing with drawers, worktop.

**Optional extras:**

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

**Colour:**

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Number of drawers	3
Drawer body usable height	225 mm

Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Drawer usable depth in G	20
Drawer usable width	500 mm
Worktop depth	750 mm
Drawer usable depth	500 mm
Drawer body depth	650 mm
Weight	133 kg
Drawer usable width in G	20
Drawer usable area in G	20×20
Height	850 mm
Series	vario
Drawer body width	600 mm
Worktop thickness	50 mm
Worktop length	2000 mm
Drawer body height	300 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

## Accessories

Drawer Drawer front height 50 mm	927800 50
Drawer Drawer front height 75 mm	927800 75
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 100 mm	927800 100
Support leg Height 800 mm	927000 800
Stabilising plate Type 1	927122 1
Worktop thickness 50 mm of beech marine ply Worktop length 2000 mm	926081 2000
Drawer casing 24G with drawers Height / number of drawers 300/3	927600 300/3