

Garant GRIDLINE

Vario workbench with drawer casing 24G, height 850 mm, Bamboo worktop, 20×20G, Worktop length: 2000/6mm



Order data

Order number	922761 2000/6
GTIN	4062406084967
Item class	9GG

Description

Version:

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height, mm: 50, 75, 100, 125, 150, 200

Supplied with:

1 × support leg, 1 × pair of stabilising plates, drawer cabinet with drawers, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer usable width	500 mm

Worktop thickness	50 mm
Drawer body height	800 mm
Drawer body depth	650 mm
Drawer usable depth	500 mm
Worktop depth	750 mm
Drawer body width	600 mm
Drawer body usable height	700 mm
Worktop length	2000 mm
Number of drawers	6
Drawer usable depth in G	20
Drawer usable width in G	20
Series	vario
Drawer usable area in G	20×20
Weight	167 kg
Height	850 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 150 mm	927800 150
Drawer Drawer front height 50 mm	927800 50
Drawer Drawer front height 125 mm	927800 125
Drawer Drawer front height 200 mm	927800 200
Drawer Drawer front height 75 mm	927800 75
Support leg Height 800 mm	927000 800
Drawer casing 24G with drawers Height / number of drawers 800/6	927600 800/6
Stabilising plate Type 1	927122 1
Worktop thickness 50 mm of bamboo strips glued cross-wise Worktop length 2000 mm	926001 2000