


Garant GRIDLINE

Vario workbench with drawer casing 24G, height 950 mm, Eluplan worktop, dark, 20×20G, Worktop length: 2000/5mm**Order data**

Order number	922717 2000/5
GTIN	4062406084936
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height, mm: 50, 75, 75, 100, 125

Supplied with:

2 × support legs, 1 × pair of stabilising plates, drawer casing with drawers, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Drawer body depth	650 mm
Drawer body usable height	425 mm

Drawer usable depth in G	20
Series	vario
Drawer usable width in G	20
Drawer body width	600 mm
Worktop length	2000 mm
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Height	950 mm
Number of drawers	5
Worktop thickness	50 mm
Weight	156 kg
Drawer usable width	500 mm
Drawer usable area in G	20×20
Drawer body height	500 mm
Worktop depth	750 mm
Drawer usable depth	500 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Drawer Drawer front height 125 mm	927800 125
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 50 mm	927800 50
Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 75 mm	927800 75
Drawer casing 24G with drawers Height / number of drawers 500/5	927600 500/5
Worktop with dark grey plastic coating (Eluplan) Worktop length 2000 mm	926241 2000
Stabilising plate Type 1	927122 1
Support leg Height 900 mm	927000 900