

Garant GRIDLINE

Vario workbench with drawer casing 24G, height 850 mm, Bamboo worktop, 20x20G, Worktop length: 1500/7mm**Order data**

Order number	922761 1500/7
GTIN	4062406084950
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height, mm: 75, 75, 75, 75, 100, 100, 200

Supplied with:

1 × support leg, 1 × pair of stabilising plates, drawer cabinet with drawers, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Worktop length	1500 mm
Drawer body depth	650 mm

Drawer body height	800 mm
Drawer usable depth	500 mm
Drawer usable width in G	20
Drawer body usable height	700 mm
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer usable width	500 mm
Drawer usable area in G	20×20
Height	850 mm
Worktop depth	750 mm
Worktop thickness	50 mm
Number of drawers	7
Drawer body width	600 mm
Weight	160 kg
Series	vario
Drawer usable depth in G	20
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Drawer Drawer front height 75 mm	927800 75
Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 200 mm	927800 200
Stabilising plate Type 1	927122 1
Drawer casing 24G with drawers Height / number of drawers 800/7	927600 800/7
Support leg Height 800 mm	927000 800
Worktop thickness 50 mm of bamboo strips glued cross-wise Worktop length 1500 mm	926001 1500