

Garant GRIDLINE

Vario workbench with drawer casing 24G, height 950 mm, Bamboo worktop, 20x20G, Worktop length: 2000/7mm**Order data**

Order number	922771 2000/7
GTIN	4062406085094
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer casing 24G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height, mm: 75; 75; 100; 100; 100; 150; 200

Supplied with:

1 × support leg, 1 × pair of stabilising plates, drawer cabinet with drawers, worktop.

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Series	vario
Weight	179 kg

Drawer usable depth	500 mm
Drawer usable width	500 mm
Drawer usable width in G	20
Drawer body usable height	800 mm
Drawer body width	600 mm
Worktop thickness	50 mm
Number of drawers	7
Height	950 mm
Worktop depth	750 mm
Drawer body height	900 mm
Drawer body depth	650 mm
Worktop length	2000 mm
Drawer usable area in G	20×20
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer usable depth in G	20
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

Accessories

Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 150 mm	927800 150
Drawer Drawer front height 200 mm	927800 200
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 75 mm	927800 75
Support leg Height 900 mm	927000 900
Worktop thickness 50 mm of bamboo strips glued cross-wise Worktop length 2000 mm	926001 2000
Stabilising plate Type 1	927122 1
Drawer casing 24G with drawers Height / number of drawers 900/7	927600 900/7