

Garant GRIDLINE

**Vario workbench with drawer casing 24G, cupboard, height 850 mm, Beech marine ply worktop, 20×20G, Worktop length: 1500/T2mm****Order data**

Order number	922784 1500/T2
GTIN	4062406085414
Item class	9GG

**Description****Version:**

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Casing 24G can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

**Fitted with:**

Drawer front height, mm: 75#75

Door height, mm: 525

Number of height-adjustable storage shelves: 1

**Supplied with:**

1 pc. support leg, 1 pc. pair of stabilising plates, casing with drawers and door, worktop.

**Colour:**

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Drawer body depth	650 mm
Drawer body height	800 mm

Drawer body width	600 mm
Drawer usable depth	500 mm
Drawer usable width	500 mm
Worktop thickness	50 mm
Worktop depth	750 mm
Worktop length	1500 mm
Number of drawers	2
Series	vario
Drawer usable area in G	20×20
Height	850 mm
Drawer usable depth in G	20
Drawer usable width in G	20
Drawer body usable height	700 mm
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Weight	119 kg
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Door opening angle	180 degrees
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench

## Accessories

Drawer Drawer front height 75 mm	927800 75
Slide handle for GridLine Type KO12	914226 KO12
Lock plate for GridLine Type KO21	914227 KO21
Support leg Height 800 mm	927000 800
Stabilising plate Type 1	927122 1
Casing 24G with door hinged on the right / drawers Height / number of drawers 800/2	927610 800/2
Worktop thickness 50 mm of beech marine ply Worktop length 1500 mm	926081 1500